




KERN load cell 150 kg

Product Images



Description

- Accuracy according to OIML R60 C3 class C3
- Dust and splash water protection IP67 (according to EN 60529), hermetically welded
- Nickel plated steel
- Application: for tension and compression force measurements
- Suitable for hanging scales, hopper scales and other weighing devices as well as force measurements and test benches
- 4-wire connection
- Note: EX version and accuracy class C4 on request
- Nominal characteristic value: 2 mV/V

Additional Information

No.	KP-3915
Manufacturer (Brand)	KERN
EAN	4058072135935
Manufacturer	KERN

