



KERN load cell 1.500 t

Product Images



Description

- Accuracy according to OIML R60 C3
- CE and RoHS compliant
- Dust and splash water protection IP68/IP69K (according to EN 60529), hermetically welded
- Stainless steel
- Application area: Mass as well as pressure force measurements under harsh environmental conditions
- Suitable for platform scales, hopper scales, scales embedded in the floor and other weighing equipment
- 4-wire connection
- Nominal sensitivity: 2 mV/V
- Note: Accuracy class OIML R60 C6 or EX version on request

Additional Information

No.	KP-3556
Manufacturer (Brand)	KERN
EAN	4058072134754
Manufacturer	KERN

