



neolab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>
e

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



Binder FED series - drying and heating cabinets Avantgarde.Line with convection and extended time functions, 115 L

€3,467.00
plus VAT &
Shipping

Product Images



Description

FED Avantgarde.Line series | Drying and heating chambers with convection and extended time functions

A BINDER heating oven of the FED Avantgarde.Line series offers almost unlimited performance and is particularly adaptable. Extended time functions and an adjustable fan allow ideal control of temperature and circulating air conditions.

Advantages

- Best energy efficiency on the market
- Very good temporal and spatial temperature accuracy
- USB connection for data recording
- Temperature range up to +300 °C

Important features

- Temperature range: +10 °C above ambient to +300 °C
- Up to 30% more energy efficient than commercially available devices
- High temperature accuracy due to APT.line™ technology
- Adjustable fan speed
- Controller with LCD display and advanced time functions
- Electromechanical control of the exhaust air damper
- 2 chrome-plated slide-in grids
- Stackable units up to 115 L
- Integrated temperature selector limiter class 2 (DIN 12880) with visual alarm
- Ergonomic handle design
- Ethernet interface
- USB port for data recording

Additional Information

No.	BB-1220
Manufacturer (Brand)	Binder
EAN	4058072522353
Transport temperature	Room temperature
Color	red grey
Temp MAX	300 °C
Wide	710 mm
Width/inside	550 mm
Height	705 mm
Height inside	550.0 mm
Depth	605 mm
Depth inside	385 mm
Number of shelves/ grids	2
Display (reading, setting)	digital
Operation via	Knobs/Buttons
Weight	57 kg
Voltage	230 V
Type interface	USB Ethernet
Heaters and warming cabinets features	with infinitely variable temperature control with timer with interface with alarm function Temp MIN/MAX depends on ambient temperature
Power	1300 W
Type of convection	Circulating air
Useful volume	116000 ml
Loading	from the front
Temp. accuracy	+/- 0.3 °C
Page door suspension	right
Temp MIN above ambient temperature	10 °C
Type tempering cabinet	Drying cabinet

