



neoLab Migge GmbH  
Rischerstr. 7-9  
69123 Heidelberg  
Deutschland  
+49 (0)6221 /  
8442-44  
<https://www.neolab.de>  
e

Umsatzsteuer-  
Identifikationsnummer  
:  
DE 143 450 657



## Binder FED series - drying and heating cabinets Avantgarde.Line with convection and extended time functions, 240 L

**€5,058.00**  
**plus VAT &**  
**Shipping**

### Product Images



## Description

---

### **FED Avantgarde.Line series | Drying and heating chambers with convection and extended time functions**

A BINDER heating oven of the FED Avantgarde.Line series offers almost unlimited performance and is particularly adaptable. Extended time functions and an adjustable fan allow ideal control of temperature and circulating air conditions.

#### **Advantages**

- Best energy efficiency on the market
- Very good temporal and spatial temperature accuracy
- USB connection for data recording
- Temperature range up to +300 °C

#### **Important features**

- Temperature range: +10 °C above ambient to +300 °C
- Up to 30% more energy efficient than commercially available devices
- High temperature accuracy due to APT.line™ technology
- Adjustable fan speed
- Controller with LCD display and advanced time functions
- Electromechanical control of the exhaust air damper
- 2 chrome-plated slide-in grids
- Stackable units up to 115 L
- Integrated temperature selector limiter class 2 (DIN 12880) with visual alarm
- Ergonomic handle design
- Ethernet interface
- USB port for data recording

## Additional Information

|                                       |  |
|---------------------------------------|--|
| No.                                   | BB-1224  |
| Manufacturer (Brand)                  | Binder   |
| EAN                                   | 4058072522391  |
| Transport temperature                 | Room temperature   |
| Color                                 | red grey   |
| Temp MAX                              | 300 °C   |
| Wide                                  | 810 mm   |
| Width/inside                          | 650 mm   |
| Height                                | 940 mm   |
| Height inside                         | 780.0 mm   |
| Depth                                 | 760 mm   |
| Depth inside                          | 515 mm   |
| Number of shelves/ grids              | 2  |
| Display (reading, setting)            | digital  |
| Operation via                         | Knobs/Buttons  |
| Weight                                | 84 kg  |
| Voltage                               | 230 V  |
| Type interface                        | USB Ethernet   |
| Heaters and warming cabinets features | with infinitely variable temperature control with timer with interface with alarm function Temp MIN/MAX depends on ambient temperature |
| Type of convection                    | Circulating air  |
| Loading                               | from the front   |
| Power                                 | 2300 W   |
| Useful volume                         | 259000 ml  |
| Page door suspension                  | right  |
| Temp MIN above ambient temperature    | 10 °C  |
| Temp. accuracy                        | +/- 0.4 °C   |
| Type tempering cabinet                | Drying cabinet   |

