



neolab Migge GmbH  
Rischerstr. 7-9  
69123 Heidelberg  
Deutschland  
+49 (0)6221 /  
8442-44  
<https://www.neolab.de>  
e

Umsatzsteuer-  
Identifikationsnummer  
:  
DE 143 450 657



## Binder FED series - Classic.Line drying and heating ovens with convection and extended time functions, 720 L

**€8,695.00**  
**plus VAT &**  
**Shipping**

### Product Images



## Description

---

### **FED Avantgarde.Line series | Drying and heating chambers with convection and extended time functions**

A BINDER heating oven from the FED Avantgarde.Line series offers virtually unlimited performance and is particularly adaptable. Extended time functions and an adjustable fan allow ideal control of temperature and circulating air conditions.

#### **Advantages**

- Best energy efficiency on the market
- Very good temporal and spatial temperature accuracy
- USB connection for data recording
- Temperature range up to +300 °C

#### **Important features**

- Temperature range: +10 °C above ambient to +300 °C
- Up to 30% more energy efficient than commercially available devices
- High temperature accuracy due to APT.line™ technology
- Adjustable fan speed
- Controller with LCD display and advanced time functions
- Electromechanical control of the exhaust air damper
- 2 chrome-plated slide-in grids
- Stackable units up to 115 L
- Integrated temperature selector limiter class 2 (DIN 12880) with visual alarm
- Ergonomic handle design
- Ethernet interface
- USB port for data recording

## Additional Information

No.	BB-1227
Manufacturer (Brand)	Binder
EAN	4058072522421
Transport temperature	Room temperature
Color	red grey
Temp MAX	300 °C
Wide	1165 mm
Width/inside	1000 mm
Height	1590 mm
Height inside	1300.0 mm
Depth	870 mm
Depth inside	570 mm
Heaters and warming cabinets features	with infinitely variable temperature control with timer with interface with alarm function Temp MIN/MAX depends on ambient temperature
Number of shelves/ grids	2
Display (reading, setting)	digital
Type of convection	Circulating air
Operation via	Knobs/Buttons
Loading	from the front
Weight	162 kg
Power	4500 W
Useful volume	741000 ml
Page door suspension	right
Voltage	208 V
Temp MIN above ambient temperature	12 °C
Temp. accuracy	+/- 0.5 °C
Type interface	USB Ethernet
Type tempering cabinet	Drying cabinet

