



neolab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>
e

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



2mag magnetic stirrer luMIX, bright luminous surface, up to 3000 ml, suitable for viscous media, 100-2000 rpm, int. control

**€1,041.00
plus VAT &
Shipping**

Product Images



Description

Ultra-flat, wear-free magnetic stirrer with large, brightly illuminated footprint, up to 3,000 ml stirring volume, also suitable for viscous media. Light and stirring function can be switched on individually. Light - Bright and seamlessly integrated heat-free light plate made of PMMA, white LEDs with homogeneous brightness and variable light intensity (4-stage), glare-free sample illumination. Stirring - 100% wear- and maintenance-free 2mag induction drive for powerful mixing of solutions, wide speed range from 100 to 2,000 rpm, jerk-free stirring even at low speeds, power setting (4-stage) for high power for large and viscous stirring volumes and reduced power for continuous operation without heating. Digital display for light, speed and power setting, SoftStart for reliable catching/centering and safe acceleration of the stirring staff, QuickSet for fast setting of initial or maximum speed. Memory of last functional state at power off, fully potted stainless steel housing, easy to clean and consistent quality. 3 years warranty on all material and manufacturing defects, developed and made in Germany. Number of stirring positions: 1 Stirring quantity: 1 - 3,000 ml Speed range: 100 - 2,000 rpm Stirring power (max.): 20 W Power setting: 4-stage (25/50/75/100%) Light setting: 4-stage (25/50/75/100%) Housing material: Stainless steel LED plate material: PMMA Seal material: PUR Perm. Operating temperature: -10 to +40 °C (at 80% humidity) Perm. storage conditions: -40 °C to +70 °C, 10 - 95%, 500 - 1060 hPa Connected load: 100-240 V / 50-60 Hz / 1.5 A Protection class: IP65 Dimensions (WxDxH): 188 x 238 x 44 mm Shipping weight (gross): approx. 4.4 kg

Additional Information

No.	ZU-0012
Manufacturer (Brand)	2mag
VGKL number	101853011
EAN	4058072444587
Gross weight	4.4
Storage temperature	Room temperature
Transport temperature	Room temperature
Net weight	4.20000 kg
Speed MAX	2000 rpm
Country of origin	Germany
Region of origin	Bavaria
Packing width	0.29000 m
Packing height	0.15000 m
Wide	188 mm
Packing depth	0.24000 m
Packaging volume	0.01044000 ccm
Customs tariff number	84798200
Height	44 mm
Depth	238 mm
Voltage	230 V
for ambient temperature	-10 to 40 °C
Drive	Magnetic field drive
Speed MIN	100 rpm
Number of stirring points	1
Protection class	IP 65
Stirring volume/stirring point MAX	3000 ml

