



neolab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>
e

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



2mag magnetic stirrer maxMIX, 1 stirring point up to 150 l, 100-1200 rpm, int. control

€2,891.00
plus VAT &
Shipping

Product Images



Description

Designed for chemical and biotechnical applications of all kinds, e.g. in quality assurance and pilot plant stations, developed for high demands, unbeatably powerful as well as for uncompromising continuous operation. Unbeatably powerful magnetic stirrer with large footprint, up to 150 liters stirring volume, also suitable for highly viscous media, very powerful magnetic coupling due to SmCo magnets, therefore predestined for power transmission over longer distances, for thick vessel bottoms or for double jacketed vessels. Maintenance-free 2mag motor drive with wide speed range from 100 to 1,200 rpm. Fully potted and sealed stainless steel housing, IP64, extremely robust design and construction, easy to clean and maximum durability, custom dimensions on request. Integrated control with powerful 40 W stirring power, wide speed range from 100 to 1,200 rpm, adjustable SoftStart function (20-99 s) for reliable catching/centering and safe acceleration of the stirring staff at different volumes and viscosities Digital display for speed and SoftStart setting, QuickSet for fast setting of initial or maximum speed, QuickStop function against overrun and glass breakage, saving of last functional state when switched off, durable stainless steel housing, easy to clean. 3 years warranty on all material and manufacturing defects, developed and made in Germany. Number of stirring positions: 1 Stirring volume: 1 - 150 liters Speed range: 100 - 1,200 rpm Stirring power (max.): 40 W Power setting: none Acceleration: variable, 20 - 99 s Material housing: stainless steel Material sealing: PUR Perm. Operating temperature: -10 to +50 °C (at 80% humidity) Perm. storage conditions: -40 °C to +70 °C, 10 - 95 %, 500 - 1060 hPa Connected load: 100-240 V / 50-60 Hz / 4.2 A Protection class: IP64 Dimensions (WxDxH): 265 x 320 x 68 mm Shipping weight (gross): approx. 10 kg

Additional Information

No.	ZU-0011
Manufacturer (Brand)	2mag
VGKL number	101853501
EAN	4058072444570
Gross weight	10
Storage temperature	Room temperature
Transport temperature	Room temperature
Net weight	9.30000 kg
Speed MAX	1200 rpm
Country of origin	Germany
Region of origin	Bavaria
Packing width	0.40000 m
Packing height	0.21000 m
Wide	265 mm
Packing depth	0.40000 m
Packaging volume	0.03360000 cc
Customs tariff number	84798200
Height	68 mm
Depth	320 mm
Voltage	230 V
for ambient temperature	-10 to 50 °C
Drive	E-motor with brushes
Speed MIN	100 rpm
Number of stirring points	1
Protection class	IP 64
Stirring volume/stirring point MAX	150000 ml

