



Julabo SW23 shaking water bath

Product Images



Description

JULABO shaking water baths convince in daily practice with numerous well thought-out details. For example, water residues are always returned to the stainless steel bath vessel via the inward sloping bath rim - even after opening the bath cover. Bath vessel: Stainless steel Bath cover: Accessories Medium bath opening (cm/WxD/BD): 50 x 30 / 18 Product features: - Working temperature range from +20 to +99.9 °C - Easy operation with membrane keypad - Bright LED display - Splash water protection all around - Power switch integrated in the operating foil (DBGM) - High temperature consistency of ± 0.2 °C or ± 0.02 °C - Dry-running protection with audible and visual signal - Warning and switch-off functions for over/under temperature - Adjustable shaking frequency 20...200 rpm - Drain screw for emptying - Removable base plate and shaker insert - Hinged bath cover (accessory) - Extensive selection of accessories for sample temperature control - All parts coming into contact with the temperature control liquid are made of stainless steel or high-quality plastics Performance data: For temperature control tasks near or below ambient temperature: use cooling coil or JULABO immersion cooler.

Additional Information

No.	JN-0503
Manufacturer (Brand)	Julabo
VGKL number	443500323
EAN	4058072848538
Net weight	20.70000 kg
Country of origin	Deutschland
Customs tariff number	84198998

