



neolab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>
e

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



CARLO ERBA CytoFAST Elite 215 safety cabinet

**Price on
request
plus VAT &
Shipping**

Product Images

Description

The **CytoFAST Elite** is a **Class II cytostatic safety cabinet**

The CytoFAST Elite has been designed and developed both to protect the material to be treated from contamination and to protect personnel and the environment from toxic substances and other harmful agents. The CytoFAST Elite cytostatic safety cabinets comply with the requirements of EN12469:2000 and DIN 12980:2017.

Features:

- Energy consumption < 351 W
- Low noise level < 53 dB(A)
- Low CO2 emission
- Hinged motorized front window for optimal cleaning
- Safety glass side windows
- Stainless steel workspace
- Segmented stainless steel work surface
- Multifunction display with PLC control
- Ergonomic design

Standard equipment:

- Motorized and completely hinged front window for optimal cleaning
- 1x vacuum tap
- 1x gas tap with safety solenoid valve for automatic shut-off
- 1 or 2 sockets depending on size

Accessories:

Electrical sockets and media connections:

- Electrical sockets, Europe / Worldwide
- Media connections (air, gas, vacuum, etc.)
- Europe / Worldwide Model DIN 12898, DIN 12919, DIN 3537

Germicidal UV lamp:

- Controlled by an automatic UV timer via the microprocessor-controlled control panel
- Radiation of 253.7 nanometers provides highly efficient decontamination
- Mounted out of the user's line of sight, for good and safe irradiation of the inner surfaces of the work area

Ergonomic footrest:

- Inclined at an angle, supports good posture
- Adjustable height
- Anti-slip coating
- Chemical resistant

Model / Type	CytoFAST Elite 0.9	CytoFAST Elite 1.2	CytoFAST Elite 1.5	CytoFAST Elite 1.8
Standards	m	m	m	m
Dimensions W×H×D (mm)	EN12469, EN61010-1 1045 × 2345 × 855	EN12469, EN61010-1 1350 × 2345 × 855	EN12469, EN61010-1 1655 × 2345 × 855	EN12469, EN61010-1 1960 × 2345 × 855
Usable dimensions W×H×D (mm)	887 × 740 × 580	1192 × 740 × 580	1497 × 740 × 580	1802 × 740 × 580
Inflow (m/s)	0.50	0.50	0.50	0.50
Downflow (m/s)	0.45 GMP	0.45 GMP	0.45 GMP	0.45 GMP
Elec. connection	230 V 50 Hz	230 V 50 Hz	230 V 50 Hz	230 V 50 Hz

Additional Information

No.	LK-0279
Manufacturer (Brand)	CARLO ERBA
EAN	4058072988678

