



neolab Migge GmbH  
Rischerstr. 7-9  
69123 Heidelberg  
Deutschland  
+49 (0)6221 /  
8442-44  
<https://www.neolab.de>  
e

Umsatzsteuer-  
Identifikationsnummer  
:  
DE 143 450 657



---

## CARLO ERBA safety workbench SafeFAST Classic 215 S

**Price on  
request  
plus VAT &  
Shipping**

### Product Images

---

# Description

## The SafeFAST Classic safety workbench is the all-rounder among the FASTER workbenches!

It is designed and manufactured to meet the requirements of the European standard EN 12469:2000 and has the highest product and personal protection. The work surface is completely made of stainless steel 1.4404 and the back panel is powder-coated, making the SafeFAST Classic ideal for use with acids, among other things. FASTER safety workbenches are designed for GMP-compliant manufacturing with hazardous substances, among other things.

### Features:

- Energy consumption <257 W
- Low noise level <53 dB(A)
- Cost-effective safety cabinet
- Optimal performance
- Motorized front window
- Safety glass side windows
- Powder coated rear panel
- Multifunction display with PLC control
- Ergonomic design
- Segmented stainless steel work surface
- Available with single blower or double blower

### Operating principle:

- 70 % recirculating via the main HEPA filter H14
- 30 % via the exhaust air HEPA filter H14

### Fields of application:

- Microbiology
- Virology
- Hematology
- Cell cultures
- Genetics

### Optional equipment:

- Hinged front window
- Double blower
- Connections for gas, vacuum, nitrogen
- UV lamp
- Electrically height adjustable base
- Weighing worktop
- Media connections
- Particle monitoring
- Arm rest
- Draft-free exhaust air connection
- Special coatings
- Touch screen monitor
- Perforated work surface or work tray

Model / Type	SafeFAST Classic 0.9 m	SafeFAST Classic 1.2 m	SafeFAST Classic 1.5 m	SafeFAST Classic 1.8 m
Standards	EN12469, EN61010-1	EN12469, EN61010-1	EN12469, EN61010-1	EN12469, EN61010-1
Dimensions W×H×D (mm)	1045 × 1500 × 810	1350 × 1500 × 810	1655 × 1500 × 810	1960 × 1500 × 810
Usable dimensions W×H×D (mm)	887 × 740 × 580	1192 × 740 × 580	1497 × 740 × 580	1802 × 740 × 580
Inflow (m/s)	0.45	0.40	0.40	0.45
Downflow (m/s)	0.40	230 V 50 Hz	230 V 50 Hz	0.40
Elec. connection	230 V 50 Hz			230 V 50 Hz

## Additional Information

---

No.	LK-0384
Manufacturer (Brand)	CARLO ERBA
EAN	4058072989729

