



neolab Migge GmbH  
Rischerstr. 7-9  
69123 Heidelberg  
Deutschland  
+49 (0)6221 /  
8442-44  
<https://www.neolab.de>  
e

Umsatzsteuer-  
Identifikationsnummer  
:  
DE 143 450 657



## Mettler-Toledo pH Meter Seven2Go S2-Standard Kit

**€715.00**  
plus VAT &  
Shipping

### Product Images



## Description

---

### Seven2Go S2 **portable pH/mV meter**

Simple and reliable with attractive and rugged design. Very good measurement quality everywhere and at all times. The new Seven2Go portable meters offer the operator fast, high-quality results, one-handed operation and high durability, making them ideal for mobile applications in the laboratory, on the production floor and outdoors. Your mobile lab for any location.

Intuitive routine instrument (IP67) for mobile pH measurement in the laboratory, production and outdoors with a wide range of functions.

With T-pad keys for convenient and fast navigation.

- Very simple, intuitive operation, robust and ergonomic design
- large multifunction display: everything at a glance
- ISM ® (intelligent sensor management), reduced risk of errors
- data logger for 200 data sets
- 5-point calibration, autom. buffer recognition/4 predefined buffer groups
- water and dust protected (IP67)
- Operation: AA batteries or rechargeable batteries

Including electrode inLab® Expert Pro (ISM version)

## Additional Information

No.	TD-0123
Manufacturer (Brand)	Mettler-Toledo
VGKL number	105002952
EAN	4058072983024
Transport temperature	Room temperature
autoclavable at 121°C	No
Color	whitelight gray
Material	Acrylonitrile butadiene styrene (ABS)
Temp MAX	105 °C
Temp MIN	-5 °C
Wide	70 mm
Height	35 mm
Depth	222 mm
Display (reading, setting)	Display 4.3" LCD Color
Weight	0.27 kg
for ambient temperature	0 to 40 °C
Counting and measuring devices Features	waterproof with internal calibration with integrated data memory with automatic temperature compensation (ATC) with automatic buffer recognition with sensor with limit setting with alarm function including batteries/battery pack
Resolution pH	0.01 pH
Resolution °C	0.1 °C
(Combined) functions	pH meter voltage thermometer
Energy supply	Battery Battery
Calibration type	at the touch of a button
measured size(s)	pH value mV temperature
pH MAX	20.0 pH
pH MIN	-2.0 pH
Data transmission	Cable

Shape connection	straight
Manufacturer	Mettler-Toledo OnLine
Measuring accuracy pH	1.00 pH
Measuring accuracy °C	0.5 °C
Voltage MAX	1999.000000 mV
Voltage MIN	-1999.000000 mV
Type sensor	InLab Expert Pro ISM IP67 Sensor
Type plug	BNC Cinch

