



neoLab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



Wiggens vacuum controller, measuring accuracy 0.25 mbar

€2,338.44
plus VAT &
Shipping

Product Images



Description

The precise **Wiggens DVR 480** is a multifunctional **vacuum controller** for connection to pumps or vacuum networks. They offer a wide range of measurement and control in vacuum technology and are ideally suited for applications where an accurate vacuum is essential.

The vacuum is adjustable from 0.1 to 1000 m.

The unit features a bright LED display and convenient on-touch control.

- Suitable for rotary evaporators
- Supports programming of control with up to 5 steps
- All parts in contact with gases are made of PTFE or high-strength ceramics
- High chemical resistance
- RS-232 and analog connection available
- Direct electrical control of the vacuum pump
- Suitable for continuous operation

Additional Information

| | |
|------------------------|------------------|
| No. | WI-1544 |
| Manufacturer (Brand) | Wiggens |
| old neoLab article no. | 2-9799 |
| EAN | 4058072443214 |
| Transport temperature | Room temperature |
| Operation via | Membrane keypad |
| Pressure MAX | 1.00 bar abs. |
| Pressure MIN | 0.1000 mbar abs. |
| Energy supply | Power grid |
| Measuring unit | mbar |
| for medium | Air/Gases/Vapors |
| measured size(s) | Print |

