



Hellma Hellmanex III 320.003

Product Images

Description

Hellmanex® III Type 320.003, Highly effective, alkaline concentrate for cleaning cuvettes made of glass and quartz glass and other sensitive optical parts. - Significant reduction of surface tension - Excellent rinsability - Use of special surfactants without absorption above 288 nm - Very good material compatibility, reduction of glass corrosion. The concentrate is filled in 1.4 kg PE bottles (1 l). Using the recommended concentration of 0.5 to 2% by volume results in approximately 50 - 200 l of cleaning liquid per bottle. Note: Sales unit ex works: cardboard box with 6 bottles (The safety data sheet is available on the homepage: hellma-analytics.com)

Additional Information

No.	KI-0707
Manufacturer (Brand)	Hellma

