



Testo® 760-2 - Digital multimeter

Product Images



Description

With the testo 760-2 digital handheld multimeter, you can measure electrical parameters more easily and safely than ever before. Unlike other multimeters, the testo 760-2 automatically recognizes the appropriate measured variable based on the socket assignment - thereby ruling out dangerous incorrect settings. Operation is not by rotary dial as usual, but with illuminated function keys. This allows you to control the measuring device comfortably with just one hand. The large, illuminated display clearly shows the measured values. The testo 760-2 digital multimeter has the most important functions for measuring current, voltage and resistance. Thanks to the larger measuring range, it is also possible to measure current in the μA range. And the integrated low-pass filter achieves more accurate measurement results for frequency converter-controlled motors. In addition to electrical parameters, temperatures can also be measured with this multimeter.

Additional Information

No.	TO-0710
Manufacturer (Brand)	Testo

