



## Nalgene® ALPS5000 Automatic Plate Sealer

### Product Images

---



## Description

ALPS5000 Automatic Plate Sealer Fast, reliable and quiet automatic plate sealing solution for any laboratory. Type: Plate Sealer Hertz: 50/60 Hz Voltage: 110/240 V Certification/Compliance: UL/NRTL, CE Description: Automated Plate Heat Sealer Dimensions (L x W x H): 19 x 9 x 21 in. Electrical Requirements: 110/240 V, 50/60 Hz Height (Anglo): 21 in. Length (Anglo): 19 in. Quantity per package: 1 Ea. Sealing temperature range: room temperature to 199 deg;C Weight (Anglo-American): 55 lb. Width (Anglo): 9 in. Unit Size: Each

## Additional Information

|                      |         |
|----------------------|---------|
| No.                  | CD-3629 |
| Manufacturer (Brand) | Nalgene |

