



# Christ® Beta 1-8 LSCbasic

## Product Images

## Description

Beta 1-8 LSCbasic freeze dryer, 230 V, 50 Hz, air-cooled, environmentally friendly, natural refrigerant, without vacuum pump, table-top design, integrated base plate for direct mounting of drying chamber or accessories with a diameter of 300 mm, ice condenser, ice condenser chamber and defrost water valve completely made of stainless steel, ice holding capacity max. 8 kg, ice condenser capacity max. 6kg/24h, ice condenser temperature approx. -55 °C, ice condenser chamber 11 liters, equipped with hot gas defrosting, vertical arrangement, especially suitable for freeze drying in round flasks, wide neck filter cap bottles and/or on unheated surfaces, equipped with system control LSCbasic (Lyo-Screen-Control basic): VGA-TFT color display, graphic-oriented user interface with touch screen, clear intuitive user interface with quick access to essential process data, multilingual user interface, password protection, display of maintenance intervals, display of vacuum in conjunction with vacuum measurement probe VCP 63 order no. 125488, vacuum control in conjunction with pressure control valve, order no. 125910,

## Additional Information

No.	HJ-0026
Manufacturer (Brand)	Christ
VGKL number	108622420

