



neolab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>
e

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



Lauda® Varioshake VS 30 O Shaker 230 V, 50/60 Hz

€4,180.00
plus VAT &
Shipping

Product Images



Description

LAUDA Varioshake VS 30 O Shaker 230 V; 50/60 Hz Performance features: Shaker with orbital movement, high load capacity, low noise, in compact design Shaking frequency display and adjustment digitally via LC display, in steps of 1.0 rpm, smooth start-up Display of set and actual values as well as shaking frequency by two LC displays User-friendly microprocessor technology Membrane keypad with concise symbols Timer adjustable from 1 min. to 99:59 hrs. or continuous operation Optional RS 232 interface on request Large motion table made of electrolytically galvanized, powder-coated sheet steel Four stand rods and adjusting rings for secure mounting of additional equipment Drive by an overload-protected AC motor Compact, low-wear mechanics with mass balancing for safe standing Constant speed, load-independent Excellent for continuous operation Outer housing made of electrolytically galvanized sheet steel, powder-coated Special rubber pad for good adhesion of objects on the motion table Technical data: Ambient temperature range: 10 ... 50 °C Motion table (WxD): 676 x 540 mm Power consumption max.: 0.09 kW Shaking amplitude: 32 mm Shaking frequency: 20 ... 250 1/min Load capacity max.: 30 kg Dimensions (WxDxH): 705 x 607 x 160 mm Weight: 40 kg Power plug: Power cord with angled Schuko plug (CEE7/7) Power supply: 230 V; 50/60 Hz

Additional Information

No.	LA-1284
Manufacturer (Brand)	Lauda
VGKL number	101103063
Transport temperature	Room temperature

