



neolab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>
e

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



KERN Luxmeter – internal sensor also suitable for LED.

€105.00
plus VAT &
Shipping

Product Images



Description

- For measuring the illumination of office workplaces, production workplaces, etc.
- Photo sensor: silicon diode, filtered
- Cosine correction for oblique incident light
- Data hold function for freezing the current measured value
- Rotatable sensor unit (+ 90 and -180°) for optimal alignment to the light source
- Stable protective cover for the photo sensor
- Increased service life: impact protection through delivery in soft box with light protection
- TRACK function for continuous recording of changing ambient conditions
- Peak hold function for recording the peak value
- Selectable units: fc (foot-candle), lx
- Convenient unit switching at the touch of a button
- Tripod can be attached to the rear of the housing, ¼ thread

Additional Information

| | |
|-----------------------|------------------|
| No. | KP-5485 |
| Manufacturer (Brand) | KERN |
| EAN | 4058072149994 |
| Transport temperature | Room temperature |
| Manufacturer | CORE |

