



neolab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>
e

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



2mag MAXcontrol control unit for MAXdrive

€1,675.00
plus VAT &
Shipping

Product Images

Description

Control unit for connection of MAXdrive, powerful 60 W stirring power, wide speed range from 100 to 1,200 rpm, variable SoftStart function for reliable catching/centering and safe acceleration of the stirring staff at different volumes and viscosities. Digital display for speed and SoftStart setting (variable, 20–99 s), QuickSet for fast setting of initial or maximum speed, QuickStop function against overrun and glass breakage, storage of last functional state when switched off, durable stainless steel housing, easy to clean. Interfaces (0–10 V, 4–20 mA, RS232, USB, Ethernet, OPC UA, LADS-oriented), other housings (e.g. for top hat rail mounting) and software modifications according to customer requirements on request. 3 years warranty on all material and manufacturing defects, developed and made in Germany. Speed range: 100 – 1,200 rpm Stirring power (max.): 60 W Power setting: none Acceleration: variable, 20 – 99 s Material housing: stainless steel Perm. operating temperature: 0 up to +40 °C (at 80% humidity) Perm. storage conditions: –40 °C to +70 °C, 10 – 95 %, 500 – 1060 hPa Connected load: 100–240 V/50–60 Hz/4.2 A Output voltage: 24 VDC Protection class: IP20 Dimensions (WxDxH): 200 x 175 x 51 mm Shipping weight (gross): approx. 2.0 kg

Additional Information

No.	ZU-0082
Manufacturer (Brand)	2mag
VGKL number	101859440
EAN	4058072445195
Gross weight	2
Storage temperature	Room temperature
Transport temperature	Room temperature
Net weight	1.80000 kg
Country of origin	Germany
Packing width	0.29000 m
Packing height	0.15000 m
Packing depth	0.24000 m
Packaging volume	0.01044000 ccm
Customs tariff number	90328900

