



neolab Migge GmbH
Rischerstr. 7-9
69123 Heidelberg
Deutschland
+49 (0)6221 /
8442-44
<https://www.neolab.de>
e

Umsatzsteuer-
Identifikationsnummer
:
DE 143 450 657



2mag MIXcontrol 20 RS232 control unit for MIXdrive stirring systems 20 W, RS232

€872.00
plus VAT &
Shipping

Product Images

Description

Universal control unit with RS232 interface, for connection of one MIXdrive stirrer drive, 20 W stirring power, speed range from 100 to 1,600 rpm, jerk-free stirring even at low speeds, 4-step power setting. Digital display for speed and power setting, SoftStart for reliable catching/centering and safe acceleration of the stirring staff, QuickSet for fast setting of the initial or maximum speed, saving of the last functional state when switched off, durable stainless steel housing, easy to clean. Interfaces (0-10 V, 4-20 mA, USB, Ethernet, OPC UA, LADS-oriented), other housings (e.g. for top hat rail mounting) and software modifications according to customer requirements on request. 3 years warranty on all material and manufacturing defects, developed and made in Germany. Speed range: 100 - 1,600 rpm Stirring power: 20 W Power setting: 4-stage (25/50/75/100%) Material housing: stainless steel Perm. operating temperature: 0 to +40 °C (at 80% humidity) Perm. storage conditions: -40 °C to +70 °C, 10 - 95 %, 500 - 1060 hPa Connected load: 100-240 V / 50-60 Hz / 1.5 A Output voltage: 48 VDC Protection class: IP20 Dimensions (WxDxH): 200 x 155 x 38 mm Shipping weight (gross): approx. 1.9 kg

Additional Information

No.	ZU-0076
Manufacturer (Brand)	2mag
EAN	4058072445133
Gross weight	1.9
Transport temperature	Room temperature
Storage temperature	Room temperature
Net weight	1.60000 kg
Country of origin	Germany
Packing width	0.29000 m
Packing height	0.15000 m
Packing depth	0.24000 m
Packaging volume	0.01044000 ccm
Customs tariff number	90328900

